

**DAIHAN-brand® 1.5~50ml Microprocessor Centrifuge "Cef-D50.6", Safety Interlock, Max. 4000rpm, Digital Model with 6-Holes or 12- & 24-Holes Fixed Angle Rotor, 1.5~50ml 튜브용 디지털 원심분리기 NEW**



**NEW**

Max. 4,000 rpm

**2-Year Warranty**

"Cef-D50.6" for 6 Tubes of 50ml, with 6 Holes Fixed Angle Rotor, 4000rpm

- Made in Korea
- Durable and Maintenance Free - Brushless DC Motor
- Ideal for Biology, Medicine, Pharmacology, Laboratory, etc. Various Application
- with 6-Holes or 12- & 24-Holes Fixed Angle Rotor for 1.5ml ~ 50ml Tubes ; On Adapters Adjustable 1.5/2ml, 5~7ml, 10~15ml, and 50ml
- Automatic Quick Self-Cooling by Fan
- Interchangeable Rotor
- \* Compact Design with Automatic Door Release.
- \* Easy to Use Controls and Display
- \* Self-diagnostic Function : Lid Opening, Unbalance, Over-Heat/ Current/ Voltage/ Speed
- \* Auto-balancing System for Extend Motor Life and Reduce Noise
- \* Program Memory Function : 9Set
- \* Precision Digital Timer, Set to 10Sec. / Max 30 Min
- \* Pushing the Function Key for Short Runs
- \* Rapid Deceleration due to Automatic Brake System

**Specifications & Ordering information**

Spec.		Model	"Cef-D50.6"	
			6 Holes - 50ml or 12/24 Holes - 1.5~50ml	
Fixed Angle Rotor&Capa.	Included		(1) 6Hole ; 50ml Tubes	
	Option		(2) 12Hole ; (1.5~15)ml Tubes, (3) 24Hole ; (1.5~15)ml Tubes	
Swing Rotor & Capa.	Option		(4) SR1550 ; ⑤ 4×1Hole - 50ml, ⑥ 4×3Hole - 10~15ml, ⑦ 4×4Hole : 5~7ml, ⑧+④ 4×3Hole : 1.5/2.0ml	
			(1) 6 Tubes ; 50ml	
Useful Tube size & Acceptance		When Option Fixed Angle Rotor	When Option Swing Rotor ; (4) SR1550	
		(2) 12 Tubes ; 1.5~15ml (3) 24 Tubes ; 1.5~15ml	⑤ 4 Tubes : 50ml, ⑥ 12 Tubes : 10~15ml ⑦ 16 Tubes : 5~7ml ⑧+④ 12 Tubes : 1.5/2.0ml	
Adapter and Size	Included		① 6ea×50ml Tubes, Size ; id30.7×L104mm	
	Option		When Option Fixed Angle Rotor	When Option Swing Rotor ;
			② 12/24ea×10~15ml Tubes Size ; id17.5×L95mm	⑤ 4×1Hole - 50ml Tubes
			③ 12/24ea×5~7ml Tubes Size ; id13.5×L69mm	⑥ 4×3Hole - 10~15ml Tubes
			④ 12/24ea×1.5/2ml Tubes Size ; id11×L42mm	⑦ 4×4Hole - 5~7ml Tubes
				⑧+④ 4×3Hole - 1.5/2.0ml Tubes
Speed Range (rpm) & RCF		600~4000rpm & 2,325×g (Swing Rotor ; 2,683×g)		
Motor		Brushless DC Motor		
Timer		0~30min		
Dimension & Weight		390×505×290mm, 19.8kg, Gross. 21.8kg		
Electric Reqts.		AC 230V, 50/60Hz or AC 120V, 60Hz		

Cat. No.	230V	DH.CefD0030
	120V	DH.CefD0130
Price, Each. W		

\* Other Specifications are available upon Customer's Request.

**Spare Rotor and Tube Adapters**

- DH.CefR5006 (1) 50ml 6Holes Angle Rotor "R5006" with 6ea×50ml Tube Adapter PP "TA50", idφ 30.7×L104mm, for "Cef-50.6" & "Cef-D50.6"
- DH.CefA050 ① 50ml Tube Adapter PP "TA50", idφ 30.7×L104mm, Fit to Rotor "R5006", for Centrifuge "Cef-50.6" & "Cef-D50.6"
- DH.CefA015 ② 10~15ml Tube Adapter PP "TA15", idφ 17.5×L98mm, for Centrifuge "Cef-6" & "Cef-8", and Rotor "R1512" & "R1524"

Ea. Price, W

**Optional Rotor and Tube Adapters**

- DH.CefR1512 (2) 10~15ml 12Holes Angle Rotor "R1512", with 12ea×10/15ml Tube Adapter "TA15", idφ 17.5×L98mm, for Centrifuge "Cef-50.6" & "Cef-D50.6"
- DH.CefR1524 (3) 10~15ml 24Holes Angle Rotor "R1524", with 24ea×10/15ml Tube Adapter "TA15", idφ 17.5×L98mm, for Centrifuge "Cef-50.6" & "Cef-D50.6"
- DH.CefSR1550 (4) Swing Rotor "SR1550", with Tube Adapter PP 1Hole×4ea×50ml "TA5001", 3Hole×4ea×1.5/2ml & 10~15ml "TA1503" and 4Hole×4ea×5~7ml "TA704", for Centrifuge "Cef-D50.6"
- DH.CefA007 ③ 5~7ml Tube Adapter PP "TA7", idφ 13.5×L69mm, Fit to "TA15", Tube Adapter, for Centrifuge "Cef-6", "Cef-8", "Cef-50.6", and "Cef-D50.6"
- DH.CefA002 ④ 1.5/2ml Tube Adapter PP "TA2", idφ 11×L42mm, Fit to "TA15", "TA1503" Tube Adapter, for Centrifuge "Cef-6", "Cef-8", "Cef-50.6", and "Cef-D50.6"
- DH.CefA5001 ⑤ 50ml Tube Adapter PP "TA5001", Fit to Rotor "SR1550", for Centrifuge "Cef-D50.6"
- DH.CefA1503 ⑥ 10~15ml 3Hole Tube Adapter PP "TA1503", Fit to Rotor "SR1550", for Centrifuge "Cef-D50.6"
- DH.CefA704 ⑦ 5~7ml 4Hole Tube Adapter PP "TA704", Fit to Rotor "SR1550", for Centrifuge "Cef-D50.6"

Ea. Price, W



(1) Fixed Angle Rotor ; 50ml 6Holes, "R5006"

①TA50



(2) Fixed Angle Rotor ; 10~15ml 12Holes, "R1512"

②TA15



(3) Fixed Angle Rotor ; 10~15ml 24Holes, "R1524"

②TA15



(4) Swing Rotor ; 4×50ml, 12×1.5/2ml & 10~15ml, 16×5~7ml "SR1550" Included ⑤,⑥,⑦ / Option ④

\*1.5/2ml ; ⑥+④



Optional Tube Adapters

①TA50 ②TA15

③TA7

④TA2