

SK-0330-M

Fixed Top LCD Digital Orbital Shaker



Features

- Independent LCD display for speed and time
- Compact footprint
- Provides smooth and uniform shaking
- Two options: 9.8kg (O330-M) and speed range 70-400rpm, 3.1kg (O180-S) and speed range 40-200rpm
- Continuous or timer operation mode
- Maintenance- free brushless DC motor
- Over speed detection and protection
- Wide range of optional platform for flasks, and other popular vessels

Applications

Orbital Shaker is ideal for applications like bacterial suspension, solubility studies, growth of bacteria and yeast, extraction procedures, washing procedures, diagnostics tests, hybridization, general mixing, staining & destaining, mixing, and extracting.

It is suitable for almost are ideal for almost any vessel from micro-centrifuge tubes through petri dishes and microplanes to conical flasks.

SK-0180-S

LED Digital Orbital Shaker

















Timer



Wide range of accessories

Specifications	SK-O180-S	SK-O330-M
Orbital diameter	20mm	10mm
Max. load capacity (with platform)	2kg	3kg
Motor type	Brushless DC motor	Brushless DC motor
Motor input power	20W	20W
Motor output power	16W	15W
Speed range	40-200rpm	70-400rpm
Speed display	LED	LCD
Timer display	LED	LCD
Time settings range	1min-19h59min	1min-19h59min
Voltage	100-240V,50/60Hz	100-240V,50/60Hz
Power	20W	25W
Weight	3.1kg	9.8kg
Permissible ambient temperature and humidity	5-40°C,80%RH	5-40°C,80%RH
Dimension[W × D × H]	294 × 348 × 123mm	420 × 370 × 100mm
Protection class	IP21	IP21
Work plate Dimension [W × D]	268x268mm	-

Cat. No.	Description	SK-O330-Pro	SK-L330-Pro	SK-R330-Pro	SK-D3309-Pro	SK-O180-Pro	SK-L180-Pro
 18900155	Dish platform with non-slip mat and fixed string (8pcs) Dimension[WxD]: 30x28.5cm	■	■	■	■		
 18202835	Silicone mattress for 16 x 5~15mL tubes, use with SK330.5	■	■	■	■		
 18202846	Silicone mattress for 6 x 50mL tubes, use with SK330.5	■	■	■	■		
 18900185	Dish attachment with non-slip mat Dimension[WxD]: 24x21.5cm					■	■
 18900200	Large size dish attachment with non-slip mat Dimension[WxD]: 30x23cm					■	■
 18900326	Dish attachment with non-slip mat Dimension[WxD]: 28x28cm					■	■
 18202852	Silicone mattress for 10 x 5~10mL tubes					■	■
 18202853	Silicone mattress for 4 x 50mL tubes					■	■
 18900027	Universal attachment with 4 bars Size: 32x32cm Capacity for flask: 25mLx21pcs, 50mLx15pcs, 100mLx12pcs, 250mLx6pcs, 500x4pcs	■	■	■	■		
 18900040	Lengthways roller attachment Size: 32x32cm Capacity for flask: 25mLx21pcs, 50mLx15pcs, 100mLx12pcs, 250mLx6pcs, 500x4pcs	■	■	■	■		
 18900025	Universal attachment with 3 bars Size: 25x24.5cm Capacity for flask: 25mLx10pcs, 50mLx8pcs, 100mLx6pcs, 250mLx4pcs, 500x2pcs					■	■
 18900038	Lengthways roller attachment Size: 25x24.5cm Capacity for flask: 25mLx10pcs, 50mLx8pcs, 100mLx6pcs, 250mLx4pcs, 500x2pcs					■	■

Cat. No.	Description	SK-O330-Pro	SK-L330-Pro	SK-R330-Pro	SK-D3309-Pro	SK-O180-Pro	SK-L180-Pro
 18900036	Bar for SK330.1 universal attachment	■	■	■	■		
 18900037	Bar for SK180.1 universal attachment					■	■
 18900280	Connect sticks for double dishes shaker	■	■	■	■	■	■
 18900028	Fixing clip attachment Size: 32 x 32cm	■	■	■	■		
 18900026	Fixing clip attachment Size: 25 x 24cm					■	■
 18900029	Fixing clip for flask volume 25mL, used with SK330.2[56pcs] SK180.2[36pcs]	■	■	■	■	■	■
 18900030	Fixing clip for flask volume 50mL, used with SK330.2[28pcs] SK180.2[18pcs]	■	■	■	■	■	■
 18900031	Fixing clip for flask volume 100mL, used with SK330.2[28pcs] SK180.2 [18pcs]	■	■	■	■	■	■
 18900032	Fixing clip for flask volume 200/250mL, used with SK330.2[13pcs] SK180.2[8pcs]	■	■	■	■	■	■
 18900033	Fixing clip for flask volume 500mL, used with SK330.2[9pcs] SK180.2[8pcs]	■	■	■	■	■	■