



designed for scientists



## MICROSTAR 15 control

/// Data Sheet

The new MICROSTAR series by IKA: Developed using the latest cutting-edge technology, this high-tech overhead stirrer with its compact design is ideal for special applications.

Combining high performance with particular excellence, they require minimum space and come with a lifetime guarantee. See for yourself:

“The Youngster” in the smallest high-tech class, moderately strong and fast!

- Hardened glass enclosed, fast response display for maximum visibility and chemical resistance



designed for scientists

- State-of-art vibration sensors detect deviations from permissible thresholds and automatically stop the process
- Clear display for all essential information at a glance
- Integrated timer / counter for the control of kinetic sensitive reactions and reminders
- Viscosities up to 8,000 mPas and volume of up to 10 l
- Continuously adjustable speed between 0/30 – 1,000 rpm
- USB interface, e.g. for documenting parameters using labworldsoft® or installing firmware updates
- Intuitive and simple handling; touch-sensitive surface for long service life
- Temperature reading on display
- Chemical resistant housing
- Key lock function
- Microprocessor-controlled speed governor for constant rotational speed, even with changes in viscosity

## Technical Data

Stirring quantity max. per stirring position (H2O) [l]	10
Motor rating input [W]	32
Motor rating output [W]	22
Motor principle	Brushless DC
Speed display	LCD
Speed min. [rpm]	30
Speed min. [rpm]	0/30
Speed max. [rpm]	1000
Viscosity max. [mPas]	8000
Output max. at stirring shaft [W]	15.7
Permissible ON time [%]	100
Torque max. at stirring shaft [Ncm]	15
Torque max. at stirring shaft at 60 1/min (overload) [Ncm]	15
Torque max. at stirring shaft at 100 1/min [Ncm]	15
Torque max. at stirring shaft at 1.000 1/min [Ncm]	15
torque I max. [Ncm]	15
Speed range I (50 Hz) [rpm]	30 - 1000
Speed range I (60 Hz) [rpm]	30 - 1000
Speed control	Turning knob
Setting accuracy speed [ $\pm$ rpm]	1
Deviation of speed measurement $n > 300$ rpm [ $\pm$ %]	1
Deviation of speed measurement $n < 300$ rpm [ $\pm$ rpm]	3
Stirring element fastening	chuck
Connection for ext. temperature sensor	PT1000
Temperature display	yes
Chuck range diameter [mm]	0.5 - 8
Hollow shaft, inner diameter [mm]	8.5
Hollow shaft (push-through - when stopped)	yes
Fastening on stand	extension arm
Extension arm diameter [mm]	13
Extension arm length [mm]	160
Torque display	yes
Speed control	electronic
Nominal torque [Nm]	0.15
Torque measurement	trend
deviation of torque measurement I [ $\pm$ Ncm]	3
Timer	yes
Timer display	LCD
Time setting range [min]	0 - 6000
Temperature measuring range [°C]	-10 - 350
Temperature measurement resolution [K]	0.1
Accuracy of temperature measurement [K]	$\pm 0.5$ + tolerance PT1000 (DIN IEC 751 Class A)
Limit deviation temperature sensor [K]	$\leq \pm (0.15 + 0.002 \times  T )$
housing material	alu-cast coating / thermoplastic polymer
communication distance (depend on building) max. [m]	150
Dimensions (W x H x D) [mm]	60 x 173 x 136
Weight [kg]	1.26
Permissible ambient temperature [°C]	5 - 40



designed for scientists

Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 54
USB interface	yes
Voltage [V]	100 - 240
Frequency [Hz]	50/60
Power input [W]	32
DC Voltage [V=]	24
Current consumption [mA]	1300

