

# IKA

designed for scientists



## C-MAG HS 4

/// Data Sheet

Magnetic stirrer with heating and ceramic heating plate which offers excellent chemical resistance.

- Powerful motor for stirring quantities of up to 5 l (H<sub>2</sub>O)
- Fixed safety circuit of 550 °C
- Hot Top indicator >> hot surface warning to prevent burns!
- Exact temperature setting via digital display (LED)
- Digital error code display
- Elevated control panel for protection against leaking liquids

[www.ika.com](http://www.ika.com)

Subject to technical changes

 IKAworldwide

 IKAworldwide /// #lookattheblue

 @IKAworldwide



designed for scientists

### Technical Data

Number of stirring positions	1
Stirring quantity max. per stirring position (H <sub>2</sub> O) [l]	5
Motor rating output [W]	1.5
Speed control	scale 0 - 6
Speed range [rpm]	100 - 1500
Heat output [W]	250
Heating temperature range [°C]	50 - 500
Heat control	LED
Heating rate heating plate [K/min]	2.5
Fixed safety circuit [°C]	550
Set-up plate material	ceramic
Set-up plate dimensions [mm]	100 x 100
Dimensions (W x H x D) [mm]	150 x 105 x 260
Weight [kg]	3
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 21
Voltage [V]	230 / 120 / 100
Frequency [Hz]	50/60
Power input [W]	270